



Product code : I0073A0000

## PISTOLET CHILTON

### DESCRIPTION

PISTOLET CHILTON is a semi-professional grade manual dispenser for the extrusion of one-component sealants and bonding products packed in cartridges.

### AREAS OF APPLICATIONS

With its solid design while remaining lightweight, PISTOLET CHILTON allows an easy and precise dispensing of one-component adhesives and sealants ranging from medium to high viscosity.

Its 360° rotating body also allows access to hard-to-reach areas without interrupting the application. It is designed for use with aluminum or PE cartridges (from 280 to 310 ml).



### TECHNICAL DATA

Nature of the materials	Body and rod in steel Handle and trigger in aluminium
Dimensions	Maximum cartridge dimensions: - Length: 218 mm - Diameter: 50 mm
Thrust ratio	18 : 1
Thrust force	2 000 N
Weight	Approx. 660 g
Advantages	Good extrusion power 360° rotating body Strong design Lightweight

### INSTRUCTIONS FOR USE

Hold the trigger on the back of the dispenser to unlock the metal rod. Manually pull the rod back, check that it is not loose and still straight to avoid pushing crooked during use.

- Aluminum cartridges: pierce the seal of the aluminum cartridge and remove, if there is one, the "easy-opening" protection system.
- PE cartridges: cut the tip of PE cartridges with a suitable tool.

Introduce the cartridge equipped with a cannula into the dispenser then press the handle to set in motion the metal rod which, by pushing on the piston, will put the cartridge into contact with the stopper and allow the extrusion of the product. Push the trigger at the back of the dispenser to stop the flow of the product.

